



### Single Section Values

Product ID	Name	Mid Section Height (in.)	Leg Section Height (in.)	Mid Section Weight (lb)	Leg Section Weight (lb)	Leg Section Depth (in.)	Mid Section Depth (in.)	Section Length (in.)	Internal Volume (gal)	Hydronic Output (BTUs)	Steam Output (BTUs)	EDR (sq. ft.)
CI-EML1-465	Emmeline I 19in	16	18.3	7.1	7.7	4.3	3.5	2.6	0.16	180	288	1.2
CI-EML1-665	Emmeline I 27in	23.9	26.2	10.0	10.6	4.3	3.5	2.6	0.21	248	396	1.65
CI-EML1-865	Emmeline I 35in	31.8	34.1	13.4	14.1	4.3	3.5	2.6	0.25	316	506	2.11
CI-EML2-470	Emmeline II 19in	16.3	18.5	9.4	11.7	6.7	5.9	2.6	0.28	244	391	1.63
CI-EML2-670	Emmeline II 27in	24.1	26.4	13.8	16.1	6.7	5.9	2.6	0.39	348	557	2.32
CI-EML2-870	Emmeline II 35in	32	34.3	18.3	20.1	6.7	5.9	2.6	0.50	452	722	3.01
CI-EML3-470	Emmeline III 19in	16.4	18.5	14.2	16.6	9.1	8.3	2.6	0.35	324	518	2.16
CI-EML3-670	Emmeline III 26in	24.3	26.4	18.7	21.8	9.1	8.3	2.6	0.47	449	718	2.99
CI-EML3-870	Emmeline III 34in	32.1	34.3	23.8	26.0	9.1	8.3	2.6	0.66	594	950	3.96
CI-G4C-360	Grace 4 Column 14in	11.8	13.8	7.1	8.2	2.4	5.7	2.4	0.15	175	281	1.17
CI-G4C-500	Grace 4 Column 20in	17.7	19.7	10.1	12.3	2.4	5.7	2.4	0.29	259	415	1.73
CI-G4C-660	Grace 4 Column 26in	23.6	25.6	12.8	13.9	2.4	5.7	2.4	0.21	339	542	2.26
CI-G4C-760	Grace 4 Column 30in	27.6	29.5	15.0	15.2	2.4	5.7	2.4	0.26	409	655	2.73
CI-G4C-960	Grace 4 Column 38in	35.4	37.4	19.8	21.2	2.4	5.7	2.4	0.29	512	818	3.41
CI-G6C-485	Grace 6 Column 19in	17.7	19.7	16.1	15.7	2.4	8.7	2.4	0.18	356	569	2.37
CI-G6C-660	Grace 6 Column 26in	23.6	25.6	18.7	19.6	2.4	8.7	2.4	0.34	483	773	3.22
CI-G6C-760	Grace 6 Column 30in	27.6	29.5	19.2	20.5	2.4	8.7	2.4	0.37	569	910	3.79
CI-G6C-960	Grace 6 Column 38in	35.4	37.4	28.4	30.0	2.4	8.7	2.4	0.40	706	1130	4.71
CI-M2C-460	Mercury 2 Column 18in	15.7	18.1	4.9	5.9	2.3	2.8	2.3	0.11	139	223	0.93
CI-M2C-760	Mercury 2 Column 30in	27.5	29.9	7.9	9.2	2.3	2.8	2.3	0.13	236	377	1.57
CI-M2C-960	Mercury 2 Column 38in	35.4	37.8	9.0	10.1	2.3	2.8	2.3	0.17	297	475	1.98
CI-M3C-560	Mercury 3 Column 22in	19.6	22	8.1	9.7	2.3	4	2.3	0.11	215	343	1.43
CI-M3C-660	Mercury 3 Column 26in	23.5	26	9.5	10.6	2.3	4	2.3	0.17	264	422	1.76
CI-M3C-760	Mercury 3 Column 30in	27.5	29.9	10.4	11.7	2.3	4	2.3	0.18	313	502	2.09
CI-M3C-860	Mercury 3 Column 34in	31.4	33.9	11.5	12.8	2.3	4	2.3	0.19	349	559	2.33
CI-M4C-360	Mercury 4 Column 14in	11.7	14.2	6.4	7.9	2.3	5.5	2.3	0.15	175	281	1.17
CI-M4C-460	Mercury 4 Column 18in	15.7	18.1	8.2	9.7	2.3	5.5	2.3	0.16	231	370	1.54
CI-M4C-560	Mercury 4 Column 22in	19.6	22	9.9	11.9	2.3	5.5	2.3	0.18	277	444	1.85
CI-M4C-760	Mercury 4 Column 30in	27.4	29.9	13.2	14.8	2.3	5.5	2.3	0.24	383	612	2.55
CI-M4C-860	Mercury 4 Column 34in	31.4	33.9	15.2	17.0	2.3	5.5	2.3	0.26	436	698	2.91
CI-M4C-960	Mercury 4 Column 38in	35.4	37.8	17.7	19.2	2.3	5.5	2.3	0.29	491	785	3.27
CI-M6C-360	Mercury 6 Column 14in	11.7	14.2	8.4	11.5	2.3	8.5	2.3	0.18	251	401	1.67
CI-M6C-960	Mercury 6 Column 38in	35.4	37.8	26.2	27.8	2.3	8.5	2.3	0.40	693	1109	4.62
CI-RC1-660	Rococo I 26in	23.3	26	13.0	15.2	3	4.5	3	0.29	275	439	1.83
CI-RC1-950	Rococo I 37in	35.2	37.4	20.1	21.8	3	4.5	3	0.34	417	667	2.78
CI-RC2-510	Rococo II 20in	17.8	20.1	13.7	17.4	3.1	7	3.1	0.48	312	499	2.08
CI-RC2-660	Rococo II 26in	22.4	26	22.1	26.0	3	7.1	3	0.53	395	631	2.63
CI-RC2-760	Rococo II 30in	27.4	29.9	24.3	27.1	3.1	7.3	3.1	0.82	459	734	3.06
CI-RC2-950	Rococo II 37in	34.6	37.4	30.6	34.0	3.1	7.1	3.1	0.82	562	900	3.75
CI-RC3-470	Rococo III 19in	16.1	18.5	18.5	20.5	3.1	8.8	3.1	0.40	329	526	2.19
CI-RC3-768	Rococo III 30in	28	30.2	26.7	29.5	3	8.9	3	0.74	559	895	3.73
CI-RC3-970	Rococo III 38in	35.2	38.2	34.2	38.6	3	8.8	3	0.92	691	1106	4.61